

SCULPTING  
PLATFORM


# CRYOLIPOLYSIS + MUSCULPTING 2 IN 1

## Fat Reduction + Muscle Building


One machine, two most popular technologies, building a perfect body



# FAT REDUCTION



# MUSCLE BUILDING



This machine integrates two of the most advanced and popular slimming and shaping technologies on the market, cryolipolysis and high-energy electromagnetic wave technology. Cryolipolysis can effectively reduce body fat, and high-energy electromagnetic wave technology has a perfect effect on shaping and muscle building. The perfect combination of the two technologies achieves the combination of fat reduction and shaping, which can create a perfect figure of the body.




-----

-----

-----

-----


# SCULPTING PLATFORM FOR THE ABDOMEN



The Musculpting Pro works on the abdomen area contracting and tightening the muscles to both burn fat and sculpt the area. This treatment can help you improve the muscle definition that you are already seeing from your fitness routine. It is also ideal for addressing that stubborn inch of fat on your stomach that just won't go away.



# FOR THE BUTTOCK



Musculpting Pro works on the buttocks as well, using the same supramaximal muscle contractions as with the abdomen area. Many patients opt to try this treatment in place of an invasive Brazilian butt lift. HIFEM technology delivers the world's first noninvasive butt lift procedure. This treatment can give you the curvature, tone, and lift that you desire. It is an alternative to the Brazilian Booty Lift procedure and provides a defined shape instead of adding excess fat to the area.

# NEW CURVED APPLICATOR CINTOIRS ARMS, THIGHS & CALVES



The Curved handle is sure to be welcomed by the thousands of men and women who want a little help with contouring the arms with stronger, more defined triceps and biceps and individuals who want to tone, lift, and sculpt the upper regions of their legs.



## SPECIFICATIONS

Cryo temperature:	-10℃~5℃(adjustable)
Sizes of handle:	A Handle: 235*65+47mm; 235*74*34mm 255*65*55mm; 255*78*40mm B Handle: 180*65*50mm; 190*65*55mm; 210+65*70mm; 220*65*80mm C Handle: 125*50*45mm; 135+50+50mm; 145*50*70mm D Handle: 83*30*50mm
Vacuum:	0-100Kpa
EMS Frequency:	1-150hz
Power:	5000w
Intensity:	7Tesla
Screen:	12.4inch
Pulse width:	310μs±10%
Cooling:	Air Cooling
Voltage:	AC220V±10% 10A 50HZ , 110v±10% 10A 60HZ

